

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212125

Luminaire Tested: **LE_4B30D010 EC4B30509040 4LBS1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212125
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509040 4LBS1H
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2884.8 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212125

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P212125

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212125

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.3	4.9
10°-20°	384.1	13.3
20°-30°	533.4	18.5
30°-40°	582.1	20.2
40°-50°	543.0	18.8
50°-60°	412.1	14.3
60°-70°	225.7	7.8
70°-80°	62.1	2.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1058.8	36.7
0°-40°	1641.0	56.9
0°-60°	2596.1	90.0
0°-90°	2884.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2884.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1509	
5°	1496	141
15°	1369	384
25°	1159	533
35°	931	582
45°	705	543
55°	460	412
65°	226	226
75°	54	62
85°	0	1
90°	0	



TEST NUMBER: P212125

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1508.7
2.5°	1508.7
5°	1496.1
7.5°	1476.9
10°	1448.4
12.5°	1410.2
15°	1368.9
17.5°	1318.1
20°	1270.5
22.5°	1213.4
25°	1159.3
27.5°	1105.4
30°	1044.9
32.5°	987.9
35°	930.7
37.5°	873.5
40°	819.4
42.5°	762.4
45°	705.2
47.5°	648.0
50°	584.4
52.5°	524.1
55°	460.5
57.5°	400.2
60°	339.9
62.5°	279.6
65°	225.5
67.5°	174.7
70°	130.3
72.5°	89.0
75°	53.9
77.5°	25.4
80°	6.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)