

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212126

Luminaire Tested: **LE_4B30D010 EC4B30509040 4LBS1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212126
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509040 4LBS1LI
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3008.3 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212126

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P212126

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212126

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.8	6.5
10°-20°	496.8	16.5
20°-30°	643.7	21.4
30°-40°	630.7	21.0
40°-50°	534.6	17.8
50°-60°	350.4	11.6
60°-70°	140.8	4.7
70°-80°	16.1	0.5
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1335.2	44.4
0°-40°	1966.0	65.3
0°-60°	2851.0	94.8
0°-90°	3008.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3008.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2148	
5°	2092	195
15°	1772	497
25°	1406	644
35°	1002	631
45°	696	535
55°	390	350
65°	136	141
75°	7	16
85°	0	0
90°	0	



TEST NUMBER: P212126

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2148.1
2.5°	2131.5
5°	2091.5
7.5°	2024.9
10°	1941.6
12.5°	1851.7
15°	1771.8
17.5°	1685.1
20°	1598.6
22.5°	1505.3
25°	1405.5
27.5°	1302.2
30°	1195.6
32.5°	1095.7
35°	1002.5
37.5°	925.8
40°	842.6
42.5°	769.3
45°	696.0
47.5°	619.4
50°	542.9
52.5°	466.2
55°	389.6
57.5°	319.7
60°	253.1
62.5°	193.1
65°	136.5
67.5°	89.9
70°	53.2
72.5°	23.3
75°	6.6
77.5°	3.4
80°	3.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)