

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211612

Luminaire Tested: **LSR4B20D010BZ EC4B10209030 4LBWMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211612  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B20D010BZ EC4B10209030 4LBWMW1  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1510.7 lumens  
Efficiency: N/A  
Efficacy: 72.6 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211612

CATALOG NUMBER: LSR4B20D010BZ EC4B10209030 4LBWMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P211612

CATALOG NUMBER: LSR4B20D010BZ EC4B10209030 4LBWMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78																			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69																			
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61																			
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55																			
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50																			
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45																			
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41																			
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38																			
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211612

CATALOG NUMBER: LSR4B20D010BZ EC4B10209030 4LBWMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.0	5.7
10°-20°	240.4	15.9
20°-30°	339.7	22.5
30°-40°	329.1	21.8
40°-50°	222.0	14.7
50°-60°	137.8	9.1
60°-70°	92.1	6.1
70°-80°	50.4	3.3
80°-90°	13.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	666.0	44.1
0°-40°	995.1	65.9
0°-60°	1354.9	89.7
0°-90°	1510.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1510.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	916	
5°	908	86
15°	853	240
25°	745	340
35°	529	329
45°	284	222
55°	151	138
65°	92	92
75°	47	50
85°	12	13
90°	0	



TEST NUMBER: P211612

CATALOG NUMBER: LSR4B20D010BZ EC4B10209030 4LBWMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	915.5
2.5°	915.5
5°	907.6
7.5°	897.8
10°	886.1
12.5°	874.3
15°	852.7
17.5°	835.1
20°	805.7
22.5°	776.3
25°	744.9
27.5°	701.8
30°	654.8
32.5°	594.0
35°	529.3
37.5°	464.6
40°	399.9
42.5°	335.2
45°	284.2
47.5°	237.2
50°	201.9
52.5°	172.5
55°	150.9
57.5°	133.3
60°	119.6
62.5°	105.9
65°	92.1
67.5°	80.4
70°	68.6
72.5°	58.8
75°	47.0
77.5°	37.2
80°	27.4
82.5°	19.6
85°	11.8
87.5°	3.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)