

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212191

Luminaire Tested: **LE_4B30D010 EC4B30509050 4LBW1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212191
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509050 4LBW1LI
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2921.2 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212191

CATALOG NUMBER: LE_4B30D010 EC4B30509050 4LBW1LI

Luminous Intensity Polar Plot





TEST NUMBER: P212191

CATALOG NUMBER: LE_4B30D010 EC4B30509050 4LBW1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			92																
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84																
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77			77																
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70			70																
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64			64																
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58			58																
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54			54																
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49			49																
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45			45																
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42			42																

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212191

CATALOG NUMBER: LE_4B30D010 EC4B30509050 4LBW1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.0	6.0
10°-20°	552.4	18.9
20°-30°	861.7	29.5
30°-40°	838.4	28.7
40°-50°	418.8	14.3
50°-60°	64.8	2.2
60°-70°	7.8	0.3
70°-80°	2.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1589.1	54.4
0°-40°	2427.5	83.1
0°-60°	2911.1	99.7
0°-90°	2921.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2921.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1790	
5°	1813	175
15°	1950	552
25°	1894	862
35°	1362	838
45°	525	419
55°	54	65
65°	7	8
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P212191

CATALOG NUMBER: LE_4B30D010 EC4B30509050 4LBW1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1789.9
2.5°	1796.6
5°	1813.3
7.5°	1840.1
10°	1873.5
12.5°	1917.0
15°	1950.4
17.5°	1977.2
20°	1980.6
22.5°	1957.2
25°	1893.6
27.5°	1799.9
30°	1682.8
32.5°	1535.6
35°	1361.6
37.5°	1170.9
40°	970.2
42.5°	756.1
45°	525.2
47.5°	337.9
50°	204.0
52.5°	110.4
55°	53.5
57.5°	23.4
60°	13.3
62.5°	10.1
65°	6.7
67.5°	6.7
70°	3.4
72.5°	3.4
75°	3.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)