

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211663

Luminaire Tested: **LSR4B20D010BZ EC4B10208035 4LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211663
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10208035 4LBSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2125.6 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211663

CATALOG NUMBER: LSR4B20D010BZ EC4B10208035 4LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P211663

CATALOG NUMBER: LSR4B20D010BZ EC4B10208035 4LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211663

CATALOG NUMBER: LSR4B20D010BZ EC4B10208035 4LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.1	3.8
10°-20°	231.3	10.9
20°-30°	348.3	16.4
30°-40°	414.5	19.5
40°-50°	413.8	19.5
50°-60°	336.5	15.8
60°-70°	207.0	9.7
70°-80°	80.2	3.8
80°-90°	12.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	660.8	31.1
0°-40°	1075.3	50.6
0°-60°	1825.5	85.9
0°-90°	2125.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2125.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	856	
5°	854	81
15°	821	231
25°	758	348
35°	664	414
45°	538	414
55°	377	336
65°	208	207
75°	73	80
85°	10	13
90°	0	



TEST NUMBER: P211663

CATALOG NUMBER: LSR4B20D010BZ EC4B10208035 4LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	856.4
2.5°	857.7
5°	853.9
7.5°	848.8
10°	842.5
12.5°	831.2
15°	821.1
17.5°	806.0
20°	789.6
22.5°	774.5
25°	758.2
27.5°	735.5
30°	712.8
32.5°	691.4
35°	663.7
37.5°	633.5
40°	605.8
42.5°	571.8
45°	537.8
47.5°	501.2
50°	462.2
52.5°	421.9
55°	376.6
57.5°	332.5
60°	289.7
62.5°	248.1
65°	207.8
67.5°	170.0
70°	134.8
72.5°	102.0
75°	73.0
77.5°	47.9
80°	29.0
82.5°	17.6
85°	10.1
87.5°	5.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)