

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170409

Luminaire Tested: **LDA4A13927D010TE LAR15SP 4LA1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170409
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25628)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A13927D010TE LAR15SP 4LA1
Description: PORTFOLIO 4" Adjustable Reflector, Self-flange Trim Ring, 15° Spot Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 909.1 lumens
Efficiency: N/A
Efficacy: 40.8 lumens/watt
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.35
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 22.27
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170409
CATALOG NUMBER: LDA4A13927D010TE LAR15SP 4LA1

Luminous Intensity Polar Plot





TEST NUMBER: P170409

CATALOG NUMBER: LDA4A13927D010TE LAR15SP 4LA1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97	97
2	112	109	106	104	110	107	105	102	104	102	100	101	100	98	98	97	96	95	95	95	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	97	95	94	92	92	92	92
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90	90	90	90
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88	88	88	88
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86	86	86	86
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84	84	84	84
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82	82	82	82
9	94	88	84	82	93	87	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80
10	92	86	82	80	91	85	82	80	85	82	80	84	81	79	84	81	79	78	78	78	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	729885
5°	608906
10°	331057
15°	175851
20°	100179
25°	19612
30°	4059
35°	1205
40°	451
45°	192
50°	115
55°	129
60°	148
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170409

CATALOG NUMBER: LDA4A13927D010TE LAR15SP 4LA1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	389.9	42.9
10°-20°	397.2	43.7
20°-30°	113.9	12.5
30°-40°	6.5	0.7
40°-50°	1.0	0.1
50°-60°	0.5	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	901.0	99.1
0°-40°	907.5	99.8
0°-60°	909.0	100.0
0°-90°	909.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	909.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5917	
5°	4918	390
15°	1377	397
25°	144	114
35°	8	6
45°	1	1
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170409

CATALOG NUMBER: LDA4A13927D010TE LAR15SP 4LA1

CANDELA DISTRIBUTION (FULL):

0°	
0°	5917.4
2.5°	5672.5
5°	4917.8
7.5°	3684.3
10°	2643.2
12.5°	1906.2
15°	1377.1
17.5°	996.7
20°	763.2
22.5°	481.2
25°	144.1
27.5°	55.2
30°	28.5
32.5°	14.8
35°	8.0
37.5°	4.6
40°	2.8
42.5°	1.7
45°	1.1
47.5°	0.6
50°	0.6
52.5°	0.6
55°	0.6
57.5°	0.6
60°	0.6
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)