

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211664

Luminaire Tested: **LSR4B20D010BZ EC4B10208035 4LBSWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211664  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B20D010BZ EC4B10208035 4LBSWH1  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2049.4 lumens  
Efficiency: N/A  
Efficacy: 98.5 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211664

CATALOG NUMBER: LSR4B20D010BZ EC4B10208035 4LBSWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P211664

CATALOG NUMBER: LSR4B20D010BZ EC4B10208035 4LBSWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |   |  |  |  |  |  |  | 20 |  |  |  |  |  |  |  |  |   |
| RC  | 80  |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30 |    |   |  |  |  |  |  |  | 10 |  |  |  |  |  |  |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 1   | 111 | 107 | 104 | 101 | 108 | 105 | 102 | 99  | 101 | 98  | 96  | 97  | 95  | 93  | 94  | 92  | 90  | 89  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 2   | 103 | 96  | 90  | 85  | 100 | 94  | 89  | 84  | 91  | 86  | 83  | 87  | 84  | 81  | 85  | 82  | 79  | 77  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 3   | 95  | 86  | 79  | 73  | 93  | 84  | 78  | 73  | 82  | 76  | 72  | 79  | 74  | 70  | 76  | 73  | 69  | 67  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 4   | 88  | 77  | 70  | 64  | 86  | 76  | 69  | 63  | 74  | 68  | 63  | 72  | 66  | 62  | 69  | 65  | 61  | 59  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 5   | 81  | 70  | 62  | 56  | 79  | 69  | 62  | 56  | 67  | 60  | 55  | 65  | 59  | 55  | 63  | 58  | 54  | 52  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 6   | 76  | 64  | 56  | 50  | 74  | 63  | 55  | 50  | 61  | 54  | 49  | 60  | 54  | 49  | 58  | 53  | 49  | 47  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 7   | 71  | 58  | 51  | 45  | 69  | 58  | 50  | 45  | 56  | 49  | 45  | 55  | 49  | 44  | 54  | 48  | 44  | 42  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 8   | 66  | 54  | 46  | 41  | 65  | 53  | 46  | 41  | 52  | 45  | 40  | 51  | 45  | 40  | 50  | 44  | 40  | 38  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 9   | 62  | 50  | 42  | 37  | 61  | 49  | 42  | 37  | 48  | 41  | 37  | 47  | 41  | 37  | 46  | 41  | 37  | 35  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 10  | 58  | 46  | 39  | 34  | 57  | 46  | 39  | 34  | 45  | 38  | 34  | 44  | 38  | 34  | 43  | 38  | 34  | 32  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211664

CATALOG NUMBER: LSR4B20D010BZ EC4B10208035 4LBSWH1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 112.7  | 5.5       |
| 10°-20°   | 291.8  | 14.2      |
| 20°-30°   | 381.6  | 18.6      |
| 30°-40°   | 404.1  | 19.7      |
| 40°-50°   | 376.9  | 18.4      |
| 50°-60°   | 285.5  | 13.9      |
| 60°-70°   | 154.6  | 7.5       |
| 70°-80°   | 41.5   | 2.0       |
| 80°-90°   | 0.6    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 786.2  | 38.4      |
| 0°-40°    | 1190.3 | 58.1      |
| 0°-60°    | 1852.6 | 90.4      |
| 0°-90°    | 2049.4 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2049.4 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1222 |      |
| 5°  | 1204 | 113  |
| 15° | 1043 | 292  |
| 25° | 830  | 382  |
| 35° | 646  | 404  |
| 45° | 491  | 377  |
| 55° | 321  | 285  |
| 65° | 155  | 155  |
| 75° | 36   | 42   |
| 85° | 0    | 1    |
| 90° | 0    |      |



TEST NUMBER: P211664

CATALOG NUMBER: LSR4B20D010BZ EC4B10208035 4LBSWH1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1222.2 |
| 2.5°  | 1217.7 |
| 5°    | 1204.3 |
| 7.5°  | 1175.1 |
| 10°   | 1137.0 |
| 12.5° | 1092.2 |
| 15°   | 1042.8 |
| 17.5° | 986.8  |
| 20°   | 937.4  |
| 22.5° | 881.3  |
| 25°   | 829.8  |
| 27.5° | 778.2  |
| 30°   | 728.9  |
| 32.5° | 686.2  |
| 35°   | 645.9  |
| 37.5° | 605.5  |
| 40°   | 567.4  |
| 42.5° | 529.3  |
| 45°   | 491.1  |
| 47.5° | 448.5  |
| 50°   | 405.9  |
| 52.5° | 363.3  |
| 55°   | 320.7  |
| 57.5° | 275.8  |
| 60°   | 233.2  |
| 62.5° | 192.9  |
| 65°   | 154.7  |
| 67.5° | 118.9  |
| 70°   | 87.5   |
| 72.5° | 60.6   |
| 75°   | 35.9   |
| 77.5° | 15.7   |
| 80°   | 4.5    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)