

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170490

Luminaire Tested: **LDA4A18930D010TE LAR15SP 4LAL1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170490
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26144)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A18930D010TE LAR15SP 4LAL1
Description: PORTFOLIO 4" Lensed Adjustable, Self-flange Trim Ring, 15° Spot
Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1422.7 lumens
Efficiency: N/A
Efficacy: 48.9 lumens/watt
Spacing Criteria (0/90/45): 0.29 / 0.29 / 0.34
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 29.12
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170490

CATALOG NUMBER: LDA4A18930D010TE LAR15SP 4LAL1

Luminous Intensity Polar Plot





TEST NUMBER: P170490

CATALOG NUMBER: LDA4A18930D010TE LAR15SP 4LAL1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97																												
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	95																												
3	109	104	101	98	107	103	100	98	101	98	96	98	96	95	96	95	93	92																												
4	106	101	97	94	104	100	96	94	98	95	93	96	94	92	94	92	91	90																												
5	103	97	94	91	102	97	93	90	95	92	90	94	91	89	92	90	88	87																												
6	100	95	91	88	99	94	90	88	93	89	87	91	89	87	90	88	86	85																												
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83																												
8	95	89	86	83	95	89	85	83	88	85	83	87	84	82	86	84	82	81																												
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79																												
10	91	85	81	79	90	85	81	79	84	81	79	83	81	79	83	80	78	78																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1189965
5°	930062
10°	507907
15°	277409
20°	156149
25°	39645
30°	7534
35°	2695
40°	1304
45°	715
50°	154
55°	172
60°	197
65°	233
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170490

CATALOG NUMBER: LDA4A18930D010TE LAR15SP 4LAL1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	593.8	41.7
10°-20°	617.1	43.4
20°-30°	193.6	13.6
30°-40°	13.6	1.0
40°-50°	3.1	0.2
50°-60°	0.7	0.1
60°-70°	0.7	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1404.5	98.7
0°-40°	1418.1	99.7
0°-60°	1422.0	100.0
0°-90°	1422.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1422.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9647	
5°	7512	594
15°	2172	617
25°	291	194
35°	18	14
45°	4	3
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170490

CATALOG NUMBER: LDA4A18930D010TE LAR15SP 4LAL1

CANDELA DISTRIBUTION (FULL):

	0°
0°	9647.4
1°	9493.7
2°	9143.0
3°	8675.9
4°	8159.3
5°	7511.6
6°	6745.2
7°	5943.7
8°	5222.8
9°	4595.5
10°	4055.2
11°	3582.5
12°	3167.5
13°	2800.6
14°	2470.2
15°	2172.4
17.5°	1568.7
20°	1189.6
22.5°	809.6
25°	291.3
27.5°	97.6
30°	52.9
32.5°	29.3
35°	17.9
37.5°	12.2
40°	8.1
42.5°	5.7
45°	4.1
47.5°	2.4
50°	0.8
52.5°	0.8
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P170490

CATALOG NUMBER: LDA4A18930D010TE LAR15SP 4LAL1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)