

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170586

Luminaire Tested: **LDA4A18930D010TE LAR15SP 4LFC1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170586
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26141)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A18930D010TE LAR15SP 4LFC1
Description: PORTFOLIO 4" Flat Cone, Self-flange Trim Ring, 15° Spot Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1553.6 lumens
Efficiency: N/A
Efficacy: 53.4 lumens/watt
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.36
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 29.12
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170586

CATALOG NUMBER: LDA4A18930D010TE LAR15SP 4LFC1

Luminous Intensity Polar Plot





TEST NUMBER: P170586

CATALOG NUMBER: LDA4A18930D010TE LAR15SP 4LFC1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97																											
2	112	109	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	95																											
3	109	104	101	98	107	103	100	98	101	98	96	98	96	95	96	95	93	92																											
4	106	101	97	94	104	100	97	94	98	95	93	96	94	92	94	92	91	90																											
5	103	98	94	91	102	97	93	91	95	92	90	94	91	89	92	90	89	88																											
6	100	95	91	88	99	94	91	88	93	90	87	92	89	87	91	88	86	85																											
7	98	92	88	86	97	92	88	86	91	87	85	90	87	85	89	86	84	83																											
8	96	90	86	83	95	89	86	83	88	85	83	88	85	83	87	84	82	81																											
9	94	88	84	81	93	87	84	81	86	83	81	86	83	81	85	82	81	80																											
10	91	85	82	79	91	85	82	79	84	81	79	84	81	79	83	81	79	78																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1213906
5°	1026379
10°	562478
15°	307047
20°	171047
25°	39523
30°	7648
35°	2198
40°	789
45°	279
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170586

CATALOG NUMBER: LDA4A18930D010TE LAR15SP 4LFC1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	652.8	42.0
10°-20°	682.9	44.0
20°-30°	204.8	13.2
30°-40°	11.8	0.8
40°-50°	1.4	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1540.5	99.2
0°-40°	1552.3	99.9
0°-60°	1553.6	100.0
0°-90°	1553.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1553.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9842	
5°	8290	653
15°	2404	683
25°	290	205
35°	15	12
45°	2	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170586

CATALOG NUMBER: LDA4A18930D010TE LAR15SP 4LFC1

CANDELA DISTRIBUTION (FULL):

	0°
0°	9841.5
1°	9744.7
2°	9569.8
3°	9335.6
4°	8930.5
5°	8289.5
6°	7496.4
7°	6633.4
8°	5831.4
9°	5098.5
10°	4490.9
11°	3964.6
12°	3496.9
13°	3092.6
14°	2730.6
15°	2404.5
17.5°	1747.2
20°	1303.1
22.5°	859.0
25°	290.4
27.5°	100.9
30°	53.7
32.5°	26.8
35°	14.6
37.5°	8.1
40°	4.9
42.5°	2.4
45°	1.6
47.5°	0.8
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P170586

CATALOG NUMBER: LDA4A18930D010TE LAR15SP 4LFC1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)