

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211683

Luminaire Tested: **LSR4B20D010BZ EC4B10209035 4LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211683
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10209035 4LBNH1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1096.5 lumens
Efficiency: N/A
Efficacy: 52.7 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211683

CATALOG NUMBER: LSR4B20D010BZ EC4B10209035 4LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P211683

CATALOG NUMBER: LSR4B20D010BZ EC4B10209035 4LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75		
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70		
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61		
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58		
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54		
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211683

CATALOG NUMBER: LSR4B20D010BZ EC4B10209035 4LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.2	11.3
10°-20°	301.3	27.5
20°-30°	349.8	31.9
30°-40°	231.7	21.1
40°-50°	65.0	5.9
50°-60°	16.3	1.5
60°-70°	6.1	0.6
70°-80°	2.1	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	775.3	70.7
0°-40°	1007.0	91.8
0°-60°	1088.3	99.2
0°-90°	1096.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1096.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1377	
5°	1341	124
15°	1079	301
25°	767	350
35°	372	232
45°	76	65
55°	18	16
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P211683

CATALOG NUMBER: LSR4B20D010BZ EC4B10209035 4LBNH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1376.7
2.5°	1370.7
5°	1340.9
7.5°	1289.3
10°	1225.7
12.5°	1154.2
15°	1078.7
17.5°	1005.2
20°	923.8
22.5°	848.3
25°	766.8
27.5°	689.3
30°	590.0
32.5°	484.7
35°	371.5
37.5°	266.2
40°	180.8
42.5°	117.2
45°	75.5
47.5°	45.7
50°	29.8
52.5°	21.9
55°	17.9
57.5°	13.9
60°	9.9
62.5°	7.9
65°	6.0
67.5°	4.0
70°	4.0
72.5°	2.0
75°	2.0
77.5°	2.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)