

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170551

Luminaire Tested: **LDA4A18835D010TE LAR35FL 4LAL1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170551
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26146)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A18835D010TE LAR35FL 4LAL1
Description: PORTFOLIO 4" Lensed Adjustable, Self-flange Trim Ring, 35° Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1953.0 lumens
Efficiency: N/A
Efficacy: 67.1 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.55
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 29.12
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170551

CATALOG NUMBER: LDA4A18835D010TE LAR35FL 4LAL1

Luminous Intensity Polar Plot





TEST NUMBER: P170551

CATALOG NUMBER: LDA4A18835D010TE LAR35FL 4LAL1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96	96	96	96
2	111	107	104	102	109	106	103	100	102	100	98	100	98	96	97	96	94	93	93	93	93
3	107	103	99	96	105	101	98	95	99	96	94	96	94	92	94	92	91	90	90	90	90
4	104	98	94	91	102	97	93	91	95	92	90	93	91	89	92	89	88	86	86	86	86
5	101	94	90	87	99	94	90	87	92	89	86	90	88	85	89	87	85	83	83	83	83
6	97	91	87	83	96	90	86	83	89	85	83	88	85	82	86	84	82	81	81	81	81
7	94	88	83	80	93	87	83	80	86	82	80	85	82	79	84	81	79	78	78	78	78
8	92	85	80	77	91	84	80	77	83	80	77	82	79	77	82	79	76	75	75	75	75
9	89	82	78	75	88	82	77	75	81	77	74	80	77	74	79	76	74	73	73	73	73
10	86	79	75	72	86	79	75	72	78	75	72	78	74	72	77	74	72	71	71	71	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	768604
5°	704542
10°	594204
15°	481826
20°	312022
25°	89960
30°	19655
35°	5571
40°	2093
45°	872
50°	384
55°	215
60°	247
65°	292
70°	361
75°	0
80°	0
85°	0



TEST NUMBER: P170551

CATALOG NUMBER: LDA4A18835D010TE LAR35FL 4LAL1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	512.7	26.3
10°-20°	1012.3	51.8
20°-30°	390.0	20.0
30°-40°	30.9	1.6
40°-50°	4.4	0.2
50°-60°	1.0	0.1
60°-70°	1.0	0.1
70°-80°	0.4	0.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1915.0	98.1
0°-40°	1945.9	99.6
0°-60°	1951.3	99.9
0°-90°	1953.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1953.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6231	
5°	5690	513
15°	3773	1012
25°	661	390
35°	37	31
45°	5	4
55°	1	1
65°	1	1
75°	0	0
85°	0	1
90°	0	



TEST NUMBER: P170551

CATALOG NUMBER: LDA4A18835D010TE LAR35FL 4LAL1

CANDELA DISTRIBUTION (FULL):

	0°
0°	6231.3
1°	6181.3
2°	6130.3
3°	6010.3
4°	5852.3
5°	5690.2
6°	5512.2
7°	5339.2
8°	5148.2
9°	4941.2
10°	4744.2
11°	4556.2
12°	4360.2
13°	4173.2
14°	3982.2
15°	3773.2
17.5°	3159.1
20°	2377.1
22.5°	1469.1
25°	661.0
27.5°	254.0
30°	138.0
32.5°	71.0
35°	37.0
37.5°	22.0
40°	13.0
42.5°	8.0
45°	5.0
47.5°	3.0
50°	2.0
52.5°	1.0
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	1.0
80°	0.0
82.5°	0.0



TEST NUMBER: P170551

CATALOG NUMBER: LDA4A18835D010TE LAR35FL 4LAL1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		1.0



(END OF REPORT)