

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211727

Luminaire Tested: **LSR4B20D010BZ EC4B10208040 4LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211727
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10208040 4LBWLI1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2077.1 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211727

CATALOG NUMBER: LSR4B20D010BZ EC4B10208040 4LBWL11

Luminous Intensity Polar Plot





TEST NUMBER: P211727

CATALOG NUMBER: LSR4B20D010BZ EC4B10208040 4LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77		
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54		
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49		
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45		
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211727

CATALOG NUMBER: LSR4B20D010BZ EC4B10208040 4LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.5	6.0
10°-20°	392.7	18.9
20°-30°	612.7	29.5
30°-40°	596.1	28.7
40°-50°	297.8	14.3
50°-60°	46.1	2.2
60°-70°	5.6	0.3
70°-80°	1.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1129.9	54.4
0°-40°	1726.0	83.1
0°-60°	2069.9	99.7
0°-90°	2077.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2077.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1273	
5°	1289	124
15°	1387	393
25°	1346	613
35°	968	596
45°	374	298
55°	38	46
65°	5	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P211727

CATALOG NUMBER: LSR4B20D010BZ EC4B10208040 4LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1272.6
2.5°	1277.4
5°	1289.3
7.5°	1308.3
10°	1332.1
12.5°	1363.0
15°	1386.8
17.5°	1405.8
20°	1408.2
22.5°	1391.6
25°	1346.4
27.5°	1279.8
30°	1196.5
32.5°	1091.8
35°	968.1
37.5°	832.6
40°	689.8
42.5°	537.6
45°	373.5
47.5°	240.3
50°	145.1
52.5°	78.5
55°	38.1
57.5°	16.7
60°	9.5
62.5°	7.1
65°	4.8
67.5°	4.8
70°	2.4
72.5°	2.4
75°	2.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)