

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170512

Luminaire Tested: **LDA4A28840D010TE LAR15SP 4LAL1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170512
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26144)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A28840D010TE LAR15SP 4LAL1
Description: PORTFOLIO 4" Lensed Adjustable, Self-flange Trim Ring, 15° Spot
Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2808.7 lumens
Efficiency: N/A
Efficacy: 63.1 lumens/watt
Spacing Criteria (0/90/45): 0.29 / 0.29 / 0.34
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 44.49
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170512

CATALOG NUMBER: LDA4A28840D010TE LAR15SP 4LAL1

Luminous Intensity Polar Plot





TEST NUMBER: P170512

CATALOG NUMBER: LDA4A28840D010TE LAR15SP 4LAL1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97				97															
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	95				95															
3	109	104	101	98	107	103	100	98	101	98	96	98	96	95	96	95	93	92				92															
4	106	101	97	94	104	100	96	94	98	95	93	96	94	92	94	92	91	90				90															
5	103	97	94	91	102	97	93	90	95	92	90	94	91	89	92	90	88	87				87															
6	100	95	91	88	99	94	90	88	93	89	87	91	89	87	90	88	86	85				85															
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83				83															
8	95	89	86	83	95	89	85	83	88	85	83	87	84	82	86	84	82	81				81															
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79				79															
10	91	85	81	79	90	85	81	79	84	81	79	83	81	79	83	80	78	78				78															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2349302
5°	1836178
10°	1002739
15°	547692
20°	308268
25°	78269
30°	14869
35°	5315
40°	2592
45°	1395
50°	307
55°	344
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170512

CATALOG NUMBER: LDA4A28840D010TE LAR15SP 4LAL1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1172.2	41.7
10°-20°	1218.4	43.4
20°-30°	382.2	13.6
30°-40°	26.9	1.0
40°-50°	6.2	0.2
50°-60°	1.4	0.1
60°-70°	1.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2772.8	98.7
0°-40°	2799.7	99.7
0°-60°	2807.4	100.0
0°-90°	2808.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2808.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19046	
5°	14830	###
15°	4289	1218
25°	575	382
35°	35	27
45°	8	6
55°	2	1
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170512

CATALOG NUMBER: LDA4A28840D010TE LAR15SP 4LAL1

CANDELA DISTRIBUTION (FULL):

	0°
0°	19046.5
1°	18742.9
2°	18050.6
3°	17128.5
4°	16108.5
5°	14829.8
6°	13316.6
7°	11734.4
8°	10311.2
9°	9072.7
10°	8006.0
11°	7072.8
12°	6253.5
13°	5529.1
14°	4876.9
15°	4289.0
17.5°	3097.0
20°	2348.5
22.5°	1598.3
25°	575.1
27.5°	192.8
30°	104.4
32.5°	57.8
35°	35.3
37.5°	24.1
40°	16.1
42.5°	11.2
45°	8.0
47.5°	4.8
50°	1.6
52.5°	1.6
55°	1.6
57.5°	1.6
60°	1.6
62.5°	1.6
65°	1.6
67.5°	1.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P170512

CATALOG NUMBER: LDA4A28840D010TE LAR15SP 4LAL1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)