

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274280

Luminaire Tested: **LD4B10DE010W2N2050 EU4B1020W2N902050 4LBW0LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274280
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35289)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBW0LI
Description: PORTFOLIO 4" W2N RN DOWNLIGHT, WIDE DISTRIBUTION WITH SPECULAR FINISH
Light Source: W2N 2000K-5000K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 846.0 lumens
Efficiency: N/A
Efficacy: 60.4 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274280

CATALOG NUMBER: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P274280

CATALOG NUMBER: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77		
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54		
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49		
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45		
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56641
5°	57603
10°	60199
15°	63899
20°	66694
25°	66113
30°	61492
35°	52606
40°	40079
45°	23502
50°	10046
55°	2953
60°	852
65°	491
70°	319
75°	422
80°	0
85°	0



TEST NUMBER: P274280

CATALOG NUMBER: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.7	6.0
10°-20°	160.0	18.9
20°-30°	249.6	29.5
30°-40°	242.8	28.7
40°-50°	121.3	14.3
50°-60°	18.8	2.2
60°-70°	2.3	0.3
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	460.2	54.4
0°-40°	703.1	83.1
0°-60°	843.1	99.7
0°-90°	846.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	846.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	518	
5°	525	51
15°	565	160
25°	548	250
35°	394	243
45°	152	121
55°	16	19
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P274280

CATALOG NUMBER: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBW0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	518.4
2.5°	520.3
5°	525.2
7.5°	532.9
10°	542.6
12.5°	555.2
15°	564.9
17.5°	572.6
20°	573.6
22.5°	566.8
25°	548.4
27.5°	521.3
30°	487.4
32.5°	444.7
35°	394.4
37.5°	339.1
40°	281.0
42.5°	219.0
45°	152.1
47.5°	97.9
50°	59.1
52.5°	32.0
55°	15.5
57.5°	6.8
60°	3.9
62.5°	2.9
65°	1.9
67.5°	1.9
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)