

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211774

Luminaire Tested: **LSR4B20D010BZ EC4B10208050 4LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211774
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10208050 4LBPSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2235.6 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211774

CATALOG NUMBER: LSR4B20D010BZ EC4B10208050 4LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P211774

CATALOG NUMBER: LSR4B20D010BZ EC4B10208050 4LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211774

CATALOG NUMBER: LSR4B20D010BZ EC4B10208050 4LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.3	3.8
10°-20°	243.3	10.9
20°-30°	366.4	16.4
30°-40°	436.0	19.5
40°-50°	435.2	19.5
50°-60°	353.9	15.8
60°-70°	217.7	9.7
70°-80°	84.3	3.8
80°-90°	13.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	695.0	31.1
0°-40°	1131.0	50.6
0°-60°	1920.0	85.9
0°-90°	2235.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2235.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	901	
5°	898	85
15°	864	243
25°	797	366
35°	698	436
45°	566	435
55°	396	354
65°	219	218
75°	77	84
85°	11	14
90°	0	



TEST NUMBER: P211774

CATALOG NUMBER: LSR4B20D010BZ EC4B10208050 4LBPSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	900.7
2.5°	902.1
5°	898.1
7.5°	892.8
10°	886.2
12.5°	874.2
15°	863.6
17.5°	847.8
20°	830.5
22.5°	814.6
25°	797.4
27.5°	773.6
30°	749.7
32.5°	727.2
35°	698.1
37.5°	666.3
40°	637.1
42.5°	601.4
45°	565.6
47.5°	527.2
50°	486.1
52.5°	443.7
55°	396.1
57.5°	349.7
60°	304.7
62.5°	260.9
65°	218.6
67.5°	178.8
70°	141.7
72.5°	107.3
75°	76.8
77.5°	50.3
80°	30.5
82.5°	18.5
85°	10.6
87.5°	5.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)