

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274283

Luminaire Tested: **LD4B10DE010W2N2765 EU4B1020W2N902765 4LBW0H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274283
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35167)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBW0H
Description: PORTFOLIO 4" W2N RN DOWNLIGHT, WIDE DISTRIBUTION WITH HAZE FINISH
Light Source: W2N 2700K-6500K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 896.0 lumens
Efficiency: N/A
Efficacy: 64.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274283

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBW0H

Luminous Intensity Polar Plot





TEST NUMBER: P274283

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBW0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63098
5°	63339
10°	63539
15°	63537
20°	63194
25°	61713
30°	57669
35°	49952
40°	39024
45°	27999
50°	18188
55°	10877
60°	6381
65°	4085
70°	2715
75°	2069
80°	1510
85°	0



TEST NUMBER: P274283

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBW0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.0	6.1
10°-20°	158.5	17.7
20°-30°	233.8	26.1
30°-40°	230.8	25.8
40°-50°	141.2	15.8
50°-60°	54.1	6.0
60°-70°	16.9	1.9
70°-80°	5.0	0.6
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	447.3	49.9
0°-40°	678.1	75.7
0°-60°	873.4	97.5
0°-90°	896.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	896.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	578	
5°	578	55
15°	562	158
25°	512	234
35°	374	231
45°	181	141
55°	57	54
65°	16	17
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P274283

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBW0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	577.5
2.5°	578.7
5°	577.5
7.5°	576.3
10°	572.7
12.5°	567.8
15°	561.7
17.5°	554.4
20°	543.5
22.5°	531.3
25°	511.9
27.5°	487.5
30°	457.1
32.5°	419.5
35°	374.5
37.5°	324.6
40°	273.6
42.5°	226.1
45°	181.2
47.5°	141.0
50°	107.0
52.5°	79.0
55°	57.1
57.5°	40.1
60°	29.2
62.5°	21.9
65°	15.8
67.5°	12.2
70°	8.5
72.5°	6.1
75°	4.9
77.5°	2.4
80°	2.4
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)