

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211803

Luminaire Tested: **LSR4B20D010BZ EC4B10209050 4LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211803
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10209050 4LBPSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1881.7 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211803

CATALOG NUMBER: LSR4B20D010BZ EC4B10209050 4LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P211803

CATALOG NUMBER: LSR4B20D010BZ EC4B10209050 4LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211803

CATALOG NUMBER: LSR4B20D010BZ EC4B10209050 4LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.8	3.8
10°-20°	204.8	10.9
20°-30°	308.4	16.4
30°-40°	367.0	19.5
40°-50°	366.3	19.5
50°-60°	297.9	15.8
60°-70°	183.2	9.7
70°-80°	71.0	3.8
80°-90°	11.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	585.0	31.1
0°-40°	951.9	50.6
0°-60°	1616.1	85.9
0°-90°	1881.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1881.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	758	
5°	756	72
15°	727	205
25°	671	308
35°	588	367
45°	476	366
55°	333	298
65°	184	183
75°	65	71
85°	9	11
90°	0	



TEST NUMBER: P211803

CATALOG NUMBER: LSR4B20D010BZ EC4B10209050 4LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	758.1
2.5°	759.3
5°	755.9
7.5°	751.4
10°	745.9
12.5°	735.8
15°	726.9
17.5°	713.5
20°	699.0
22.5°	685.7
25°	671.2
27.5°	651.1
30°	631.0
32.5°	612.1
35°	587.6
37.5°	560.8
40°	536.3
42.5°	506.2
45°	476.1
47.5°	443.7
50°	409.2
52.5°	373.5
55°	333.4
57.5°	294.3
60°	256.4
62.5°	219.6
65°	184.0
67.5°	150.5
70°	119.3
72.5°	90.3
75°	64.7
77.5°	42.4
80°	25.6
82.5°	15.6
85°	8.9
87.5°	4.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)