

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211814

Luminaire Tested: **LSR4B20D010BZ EC4B10209050 4LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211814
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10209050 4LBWLI1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1747.5 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211814

CATALOG NUMBER: LSR4B20D010BZ EC4B10209050 4LBWL11

Luminous Intensity Polar Plot





TEST NUMBER: P211814

CATALOG NUMBER: LSR4B20D010BZ EC4B10209050 4LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77			77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70			70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64			64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54			54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49			49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45			45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42			42

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211814

CATALOG NUMBER: LSR4B20D010BZ EC4B10209050 4LBWL11

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.7	6.0
10°-20°	330.4	18.9
20°-30°	515.5	29.5
30°-40°	501.6	28.7
40°-50°	250.5	14.3
50°-60°	38.8	2.2
60°-70°	4.7	0.3
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	950.6	54.4
0°-40°	1452.2	83.1
0°-60°	1741.5	99.7
0°-90°	1747.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1747.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1071	
5°	1085	105
15°	1167	330
25°	1133	515
35°	815	502
45°	314	251
55°	32	39
65°	4	5
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P211814

CATALOG NUMBER: LSR4B20D010BZ EC4B10209050 4LBWLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1070.7
2.5°	1074.7
5°	1084.8
7.5°	1100.8
10°	1120.8
12.5°	1146.8
15°	1166.8
17.5°	1182.8
20°	1184.8
22.5°	1170.8
25°	1132.8
27.5°	1076.7
30°	1006.7
32.5°	918.6
35°	814.6
37.5°	700.5
40°	580.4
42.5°	452.3
45°	314.2
47.5°	202.1
50°	122.1
52.5°	66.0
55°	32.0
57.5°	14.0
60°	8.0
62.5°	6.0
65°	4.0
67.5°	4.0
70°	2.0
72.5°	2.0
75°	2.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)