

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211830

Luminaire Tested: **LSR4B30D010BZ EC4B30509024 4LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211830
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509024 4LBNMW1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1504.4 lumens
Efficiency: N/A
Efficacy: 53.7 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211830

CATALOG NUMBER: LSR4B30D010BZ EC4B30509024 4LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P211830

CATALOG NUMBER: LSR4B30D010BZ EC4B30509024 4LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	105	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	80	96	89	83	79	86	82	78	84	80	76	81	78	75	73		
4	92	83	76	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	62	57	53	52		
8	73	62	55	50	71	61	55	50	60	54	50	59	53	49	58	53	49	48		
9	69	58	51	46	68	57	51	46	56	50	46	55	50	46	54	49	46	44		
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211830

CATALOG NUMBER: LSR4B30D010BZ EC4B30509024 4LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.1	7.8
10°-20°	308.9	20.5
20°-30°	406.6	27.0
30°-40°	316.5	21.0
40°-50°	153.7	10.2
50°-60°	97.1	6.5
60°-70°	62.6	4.2
70°-80°	32.8	2.2
80°-90°	8.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	833.6	55.4
0°-40°	1150.1	76.4
0°-60°	1400.9	93.1
0°-90°	1504.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1504.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1283	
5°	1260	118
15°	1102	309
25°	896	407
35°	507	317
45°	191	154
55°	108	97
65°	62	63
75°	31	33
85°	7	8
90°	0	



TEST NUMBER: P211830

CATALOG NUMBER: LSR4B30D010BZ EC4B30509024 4LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1283.4
2.5°	1276.2
5°	1259.5
7.5°	1230.8
10°	1192.6
12.5°	1149.6
15°	1101.8
17.5°	1051.6
20°	999.0
22.5°	948.8
25°	896.2
27.5°	829.3
30°	738.5
32.5°	630.9
35°	506.7
37.5°	392.0
40°	303.5
42.5°	236.6
45°	191.2
47.5°	155.3
50°	136.2
52.5°	121.9
55°	107.5
57.5°	95.6
60°	83.6
62.5°	71.7
65°	62.1
67.5°	55.0
70°	45.4
72.5°	38.2
75°	31.1
77.5°	23.9
80°	16.7
82.5°	11.9
85°	7.2
87.5°	2.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)