

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211843

Luminaire Tested: **LSR4B30D010BZ EC4B30509024 4LBWLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211843  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B30D010BZ EC4B30509024 4LBWLI1  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2088.0 lumens  
Efficiency: N/A  
Efficacy: 74.6 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211843

CATALOG NUMBER: LSR4B30D010BZ EC4B30509024 4LBWL11

### Luminous Intensity Polar Plot





TEST NUMBER: P211843

CATALOG NUMBER: LSR4B30D010BZ EC4B30509024 4LBWL11

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77			77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70			70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64			64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54			54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49			49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45			45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42			42

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211843

CATALOG NUMBER: LSR4B30D010BZ EC4B30509024 4LBWLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.1	6.0
10°-20°	394.8	18.9
20°-30°	615.9	29.5
30°-40°	599.3	28.7
40°-50°	299.3	14.3
50°-60°	46.3	2.2
60°-70°	5.6	0.3
70°-80°	1.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1135.9	54.4
0°-40°	1735.2	83.1
0°-60°	2080.8	99.7
0°-90°	2088.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2088.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1279	
5°	1296	125
15°	1394	395
25°	1354	616
35°	973	599
45°	375	299
55°	38	46
65°	5	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P211843

CATALOG NUMBER: LSR4B30D010BZ EC4B30509024 4LBWLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1279.4
2.5°	1284.2
5°	1296.1
7.5°	1315.2
10°	1339.2
12.5°	1370.2
15°	1394.2
17.5°	1413.3
20°	1415.7
22.5°	1398.9
25°	1353.5
27.5°	1286.5
30°	1202.9
32.5°	1097.6
35°	973.3
37.5°	837.0
40°	693.5
42.5°	540.4
45°	375.4
47.5°	241.5
50°	145.9
52.5°	78.9
55°	38.3
57.5°	16.7
60°	9.6
62.5°	7.2
65°	4.8
67.5°	4.8
70°	2.4
72.5°	2.4
75°	2.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)