

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274315

Luminaire Tested: **LD4B20DE010W2N2765 EU4B1020W2N902765 4LBCS0MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P274315  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35143)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B20DE010W2N2765 EU4B1020W2N902765 4LBCS0MB  
Description: PORTFOLIO 4" W2N RN DOWNLIGHT, CAST SHALLOW WITH MATTE BLACK FINISH  
Light Source: W2N 2700K-6500K CCT TUNING RANGE  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1445.6 lumens  
Efficiency: N/A  
Efficacy: 51.6 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Circular (Dia: 0.38' x H: 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P274315

CATALOG NUMBER: LD4B20DE010W2N2765 EU4B1020W2N902765 4LBCS0MB

### Luminous Intensity Polar Plot





TEST NUMBER: P274315

CATALOG NUMBER: LD4B20DE010W2N2765 EU4B1020W2N902765 4LBCS0MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	59488
5°	59618
10°	59179
15°	58873
20°	58255
25°	57724
30°	56920
35°	55977
40°	54184
45°	52140
50°	48715
55°	43668
60°	36761
65°	29402
70°	21257
75°	11711
80°	2301
85°	0



TEST NUMBER: P274315

CATALOG NUMBER: LD4B20DE010W2N2765 EU4B1020W2N902765 4LBCS0MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.7	4.0
10°-20°	164.5	11.4
20°-30°	247.3	17.1
30°-40°	293.4	20.3
40°-50°	290.3	20.1
50°-60°	228.1	15.8
60°-70°	127.9	8.8
70°-80°	35.9	2.5
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	469.5	32.5
0°-40°	762.9	52.8
0°-60°	1281.3	88.6
0°-90°	1445.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1445.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	610	
5°	609	58
15°	584	164
25°	537	247
35°	470	293
45°	378	290
55°	257	228
65°	128	128
75°	31	36
85°	0	1
90°	0	



TEST NUMBER: P274315

CATALOG NUMBER: LD4B20DE010W2N2765 EU4B1020W2N902765 4LBCS0MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	610.4
2.5°	608.4
5°	609.4
7.5°	604.2
10°	598.0
12.5°	590.7
15°	583.5
17.5°	574.2
20°	561.7
22.5°	549.3
25°	536.8
27.5°	523.4
30°	505.8
32.5°	488.1
35°	470.5
37.5°	449.8
40°	425.9
42.5°	403.1
45°	378.3
47.5°	350.3
50°	321.3
52.5°	288.1
55°	257.0
57.5°	221.8
60°	188.6
62.5°	158.6
65°	127.5
67.5°	100.5
70°	74.6
72.5°	50.8
75°	31.1
77.5°	15.5
80°	4.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)