

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211854

Luminaire Tested: **LSR4B30D010BZ EC4B30508027 4LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211854
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30508027 4LBMWH1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2143.6 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211854

CATALOG NUMBER: LSR4B30D010BZ EC4B30508027 4LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P211854

CATALOG NUMBER: LSR4B30D010BZ EC4B30508027 4LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	105	105	103	101	101	100	98	98	96	95	94																			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71																			
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66																			
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62																			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58																			
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55																			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211854

CATALOG NUMBER: LSR4B30D010BZ EC4B30508027 4LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	235.2	11.0
10°-20°	604.7	28.2
20°-30°	709.4	33.1
30°-40°	448.9	20.9
40°-50°	120.3	5.6
50°-60°	16.8	0.8
60°-70°	6.2	0.3
70°-80°	2.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1549.2	72.3
0°-40°	1998.1	93.2
0°-60°	2135.2	99.6
0°-90°	2143.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2143.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2546	
5°	2505	235
15°	2166	605
25°	1567	709
35°	712	449
45°	136	120
55°	16	17
65°	6	6
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P211854

CATALOG NUMBER: LSR4B30D010BZ EC4B30508027 4LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2545.8
2.5°	2536.3
5°	2504.6
7.5°	2453.9
10°	2381.1
12.5°	2286.1
15°	2165.8
17.5°	2042.3
20°	1893.5
22.5°	1741.5
25°	1567.3
27.5°	1377.4
30°	1165.2
32.5°	934.1
35°	712.4
37.5°	516.1
40°	354.6
42.5°	228.0
45°	136.2
47.5°	76.0
50°	41.2
52.5°	22.2
55°	15.8
57.5°	12.7
60°	9.5
62.5°	9.5
65°	6.3
67.5°	3.2
70°	3.2
72.5°	3.2
75°	3.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)