

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211876

Luminaire Tested: **LSR4B30D010BZ EC4B30509027 4LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211876
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509027 4LBCSMMS1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2113.3 lumens
Efficiency: N/A
Efficacy: 75.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211876

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P211876

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	83	80	78	76			76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211876

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	4.3
10°-20°	256.6	12.1
20°-30°	374.8	17.7
30°-40°	428.7	20.3
40°-50°	412.0	19.5
50°-60°	318.2	15.1
60°-70°	177.6	8.4
70°-80°	51.7	2.4
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	722.9	34.2
0°-40°	1151.6	54.5
0°-60°	1881.8	89.0
0°-90°	2113.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2113.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	970	
5°	962	91
15°	910	257
25°	815	375
35°	686	429
45°	537	412
55°	357	318
65°	178	178
75°	45	52
85°	1	2
90°	0	



TEST NUMBER: P211876

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBCSMMS1

CANDELA DISTRIBUTION (FULL):

0°	
0°	970.5
2.5°	970.5
5°	962.3
7.5°	958.2
10°	944.5
12.5°	928.1
15°	910.3
17.5°	892.6
20°	866.6
22.5°	846.1
25°	814.7
27.5°	783.2
30°	751.8
32.5°	720.3
35°	686.2
37.5°	652.0
40°	612.4
42.5°	576.8
45°	537.2
47.5°	492.1
50°	449.7
52.5°	403.2
55°	356.8
57.5°	308.9
60°	263.8
62.5°	218.7
65°	177.7
67.5°	139.4
70°	103.9
72.5°	72.4
75°	45.1
77.5°	23.2
80°	8.2
82.5°	2.7
85°	1.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)