

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211890

Luminaire Tested: **LSR4B30D010BZ EC4B30509027 4LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211890
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509027 4LBPSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2555.7 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211890

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P211890

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86	86	86	86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74	74	74	74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63	63	63	63
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54	54	54	54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47	47	47	47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42	42	42	42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37	37	37	37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33	33	33	33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30	30	30	30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27	27	27	27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211890

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.6	3.8
10°-20°	278.1	10.9
20°-30°	418.8	16.4
30°-40°	498.4	19.5
40°-50°	497.5	19.5
50°-60°	404.6	15.8
60°-70°	248.9	9.7
70°-80°	96.4	3.8
80°-90°	15.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	794.5	31.1
0°-40°	1292.9	50.6
0°-60°	2194.9	85.9
0°-90°	2555.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2555.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1030	
5°	1027	98
15°	987	278
25°	912	419
35°	798	498
45°	647	497
55°	453	405
65°	250	249
75°	88	96
85°	12	15
90°	0	



TEST NUMBER: P211890

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1029.7
2.5°	1031.2
5°	1026.7
7.5°	1020.6
10°	1013.0
12.5°	999.4
15°	987.3
17.5°	969.1
20°	949.4
22.5°	931.3
25°	911.6
27.5°	884.3
30°	857.1
32.5°	831.3
35°	798.0
37.5°	761.7
40°	728.3
42.5°	687.5
45°	646.6
47.5°	602.7
50°	555.7
52.5°	507.3
55°	452.8
57.5°	399.8
60°	348.3
62.5°	298.3
65°	249.8
67.5°	204.4
70°	162.0
72.5°	122.7
75°	87.8
77.5°	57.5
80°	34.8
82.5°	21.2
85°	12.1
87.5°	6.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)