

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210806

Luminaire Tested: **LSR4B10D010BZ EC4B10208030 4LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10208030 4LBMGPH1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 579.7 lumens
Efficiency: N/A
Efficacy: 58.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210806

CATALOG NUMBER: LSR4B10D010BZ EC4B10208030 4LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P210806

CATALOG NUMBER: LSR4B10D010BZ EC4B10208030 4LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86																			
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79																			
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73																			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																			
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63																			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59																			
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55																			
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51																			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210806

CATALOG NUMBER: LSR4B10D010BZ EC4B10208030 4LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.8	9.5
10°-20°	143.0	24.7
20°-30°	183.4	31.6
30°-40°	132.6	22.9
40°-50°	47.5	8.2
50°-60°	12.8	2.2
60°-70°	4.2	0.7
70°-80°	1.3	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	381.3	65.8
0°-40°	513.9	88.6
0°-60°	574.2	99.1
0°-90°	579.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	579.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	596	
5°	585	55
15°	509	143
25°	405	183
35°	212	133
45°	57	48
55°	13	13
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P210806

CATALOG NUMBER: LSR4B10D010BZ EC4B10208030 4LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	596.0
2.5°	593.5
5°	585.0
7.5°	571.6
10°	553.3
12.5°	532.6
15°	509.4
17.5°	486.3
20°	463.1
22.5°	436.3
25°	404.6
27.5°	368.1
30°	321.8
32.5°	268.1
35°	212.1
37.5°	160.9
40°	117.0
42.5°	82.9
45°	57.3
47.5°	39.0
50°	25.6
52.5°	18.3
55°	13.4
57.5°	9.8
60°	7.3
62.5°	6.1
65°	3.7
67.5°	2.4
70°	2.4
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)