

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211895

Luminaire Tested: **LSR4B30D010BZ EC4B30509027 4LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211895
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509027 4LBSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2455.0 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211895

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P211895

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																																				
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																																				
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																																				
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																																				
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																																				
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																																				
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																																				
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																																				
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																																				
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211895

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.7	3.8
10°-20°	267.1	10.9
20°-30°	402.3	16.4
30°-40°	478.8	19.5
40°-50°	477.9	19.5
50°-60°	388.6	15.8
60°-70°	239.1	9.7
70°-80°	92.6	3.8
80°-90°	14.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	763.2	31.1
0°-40°	1242.0	50.6
0°-60°	2108.5	85.9
0°-90°	2455.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2455.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	989	
5°	986	94
15°	948	267
25°	876	402
35°	767	479
45°	621	478
55°	435	389
65°	240	239
75°	84	93
85°	12	15
90°	0	



TEST NUMBER: P211895

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	989.1
2.5°	990.6
5°	986.2
7.5°	980.4
10°	973.1
12.5°	960.0
15°	948.4
17.5°	930.9
20°	912.0
22.5°	894.6
25°	875.7
27.5°	849.5
30°	823.3
32.5°	798.6
35°	766.6
37.5°	731.7
40°	699.7
42.5°	660.4
45°	621.1
47.5°	578.9
50°	533.8
52.5°	487.3
55°	434.9
57.5°	384.0
60°	334.6
62.5°	286.6
65°	240.0
67.5°	196.4
70°	155.6
72.5°	117.8
75°	84.4
77.5°	55.3
80°	33.5
82.5°	20.4
85°	11.6
87.5°	5.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)