

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211897

Luminaire Tested: **LSR4B30D010BZ EC4B30509027 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509027 4LBSWMH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2386.7 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211897

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P211897

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211897

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.8	5.9
10°-20°	370.5	15.5
20°-30°	497.6	20.8
30°-40°	509.3	21.3
40°-50°	440.9	18.5
50°-60°	293.2	12.3
60°-70°	120.4	5.0
70°-80°	14.3	0.6
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1007.9	42.2
0°-40°	1517.2	63.6
0°-60°	2251.3	94.3
0°-90°	2386.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2386.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1513	
5°	1489	140
15°	1323	370
25°	1086	498
35°	813	509
45°	574	441
55°	325	293
65°	119	120
75°	6	14
85°	0	1
90°	0	



TEST NUMBER: P211897

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1512.7
2.5°	1509.5
5°	1489.2
7.5°	1457.9
10°	1415.7
12.5°	1368.8
15°	1323.4
17.5°	1265.5
20°	1209.2
22.5°	1149.8
25°	1085.6
27.5°	1016.8
30°	948.0
32.5°	879.1
35°	813.4
37.5°	750.9
40°	691.4
42.5°	632.0
45°	574.1
47.5°	513.1
50°	450.5
52.5°	387.9
55°	325.4
57.5°	270.6
60°	214.3
62.5°	162.7
65°	118.9
67.5°	78.2
70°	45.4
72.5°	21.9
75°	6.3
77.5°	3.1
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)