

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211899

Luminaire Tested: **LSR4B30D010BZ EC4B30509027 4LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211899
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509027 4LBWGPH1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1568.7 lumens
Efficiency: N/A
Efficacy: 56.0 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211899

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBWGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P211899

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92																												
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83																												
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76																												
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69																												
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63																												
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57																												
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53																												
8	73	62	56	51	72	62	55	51	61	55	51	59	54	50	58	54	50	48																												
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45																												
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211899

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.5	6.8
10°-20°	301.8	19.2
20°-30°	432.8	27.6
30°-40°	407.5	26.0
40°-50°	225.1	14.3
50°-60°	72.2	4.6
60°-70°	18.1	1.2
70°-80°	4.3	0.3
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	841.2	53.6
0°-40°	1248.7	79.6
0°-60°	1546.0	98.6
0°-90°	1568.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1568.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1129	
5°	1124	106
15°	1069	302
25°	950	433
35°	661	408
45°	286	225
55°	74	72
65°	16	18
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P211899

CATALOG NUMBER: LSR4B30D010BZ EC4B30509027 4LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1129.1
2.5°	1120.9
5°	1123.6
7.5°	1115.5
10°	1101.9
12.5°	1088.3
15°	1069.2
17.5°	1052.9
20°	1025.7
22.5°	987.6
25°	949.5
27.5°	897.8
30°	829.8
32.5°	753.6
35°	661.1
37.5°	563.2
40°	462.5
42.5°	370.0
45°	285.7
47.5°	214.9
50°	155.1
52.5°	108.8
55°	73.5
57.5°	49.0
60°	35.4
62.5°	24.5
65°	16.3
67.5°	10.9
70°	8.2
72.5°	5.4
75°	2.7
77.5°	2.7
80°	2.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)