

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210839

Luminaire Tested: **LSR4B10D010BZ EC4B10209030 4LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210839
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209030 4LBMWH1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 704.1 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210839

CATALOG NUMBER: LSR4B10D010BZ EC4B10209030 4LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P210839

CATALOG NUMBER: LSR4B10D010BZ EC4B10209030 4LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	96	95	94																			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71																			
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66																			
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62																			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58																			
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55																			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210839

CATALOG NUMBER: LSR4B10D010BZ EC4B10209030 4LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.3	11.0
10°-20°	198.6	28.2
20°-30°	233.0	33.1
30°-40°	147.5	20.9
40°-50°	39.5	5.6
50°-60°	5.5	0.8
60°-70°	2.0	0.3
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	508.9	72.3
0°-40°	656.4	93.2
0°-60°	701.4	99.6
0°-90°	704.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	704.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	836	
5°	823	77
15°	712	199
25°	515	233
35°	234	147
45°	45	40
55°	5	6
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P210839

CATALOG NUMBER: LSR4B10D010BZ EC4B10209030 4LBMWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	836.3
2.5°	833.2
5°	822.8
7.5°	806.1
10°	782.2
12.5°	751.0
15°	711.5
17.5°	670.9
20°	622.0
22.5°	572.1
25°	514.9
27.5°	452.5
30°	382.8
32.5°	306.8
35°	234.0
37.5°	169.5
40°	116.5
42.5°	74.9
45°	44.7
47.5°	25.0
50°	13.5
52.5°	7.3
55°	5.2
57.5°	4.2
60°	3.1
62.5°	3.1
65°	2.1
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)