

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211937

Luminaire Tested: **LSR4B30D010BZ EC4B30508030 4LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211937
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30508030 4LBMGPH1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1575.5 lumens
Efficiency: N/A
Efficacy: 56.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211937

CATALOG NUMBER: LSR4B30D010BZ EC4B30508030 4LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P211937

CATALOG NUMBER: LSR4B30D010BZ EC4B30508030 4LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	52	49	48

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211937

CATALOG NUMBER: LSR4B30D010BZ EC4B30508030 4LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.0	9.5
10°-20°	388.7	24.7
20°-30°	498.5	31.6
30°-40°	360.3	22.9
40°-50°	129.2	8.2
50°-60°	34.9	2.2
60°-70°	11.4	0.7
70°-80°	3.5	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1036.2	65.8
0°-40°	1396.5	88.6
0°-60°	1560.6	99.1
0°-90°	1575.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1575.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1620	
5°	1590	149
15°	1385	389
25°	1100	499
35°	576	360
45°	156	129
55°	36	35
65°	10	11
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P211937

CATALOG NUMBER: LSR4B30D010BZ EC4B30508030 4LBMGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1619.8
2.5°	1613.1
5°	1589.9
7.5°	1553.5
10°	1503.8
12.5°	1447.5
15°	1384.6
17.5°	1321.6
20°	1258.7
22.5°	1185.8
25°	1099.7
27.5°	1000.3
30°	874.5
32.5°	728.7
35°	576.4
37.5°	437.2
40°	318.0
42.5°	225.2
45°	155.7
47.5°	106.0
50°	69.6
52.5°	49.7
55°	36.4
57.5°	26.5
60°	19.9
62.5°	16.6
65°	9.9
67.5°	6.6
70°	6.6
72.5°	3.3
75°	3.3
77.5°	3.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)