

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211938

Luminaire Tested: **LSR4B30D010BZ EC4B30508030 4LBMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211938  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B30D010BZ EC4B30508030 4LBMH1  
Description: PORTFOLIO 4 INCH CYLINDER  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2194.4 lumens  
Efficiency: N/A  
Efficacy: 78.4 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211938

CATALOG NUMBER: LSR4B30D010BZ EC4B30508030 4LBMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P211938

CATALOG NUMBER: LSR4B30D010BZ EC4B30508030 4LBMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93					93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85					85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79					79			
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73					73			
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67					67			
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62					62			
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58					58			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54					54			
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50					50			
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47					47			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211938

CATALOG NUMBER: LSR4B30D010BZ EC4B30508030 4LBMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	200.2	9.1
10°-20°	525.3	23.9
20°-30°	675.1	30.8
30°-40°	507.9	23.1
40°-50°	204.0	9.3
50°-60°	58.0	2.6
60°-70°	18.3	0.8
70°-80°	5.2	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1400.6	63.8
0°-40°	1908.5	87.0
0°-60°	2170.4	98.9
0°-90°	2194.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2194.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2176	
5°	2136	200
15°	1875	525
25°	1490	675
35°	815	508
45°	252	204
55°	60	58
65°	17	18
75°	3	5
85°	0	0
90°	0	



TEST NUMBER: P211938

CATALOG NUMBER: LSR4B30D010BZ EC4B30508030 4LBMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2176.0
2.5°	2162.8
5°	2136.3
7.5°	2086.6
10°	2023.7
12.5°	1947.5
15°	1874.6
17.5°	1791.8
20°	1702.4
22.5°	1606.3
25°	1490.4
27.5°	1351.3
30°	1189.0
32.5°	1006.9
35°	814.8
37.5°	635.9
40°	476.9
42.5°	351.1
45°	251.7
47.5°	172.2
50°	119.2
52.5°	82.8
55°	59.6
57.5°	43.1
60°	33.1
62.5°	23.2
65°	16.6
67.5°	13.2
70°	9.9
72.5°	6.6
75°	3.3
77.5°	3.3
80°	3.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)