

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210865

Luminaire Tested: **LSR4B10D010BZ EC4B10209730 4LBMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P210865  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B10D010BZ EC4B10209730 4LBMH1  
Description: PORTFOLIO 4 INCH CYLINDER  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W  
DL3-11.1W DLE-11.39W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 602.5 lumens  
Efficiency: N/A  
Efficacy: 60.9 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P210865

CATALOG NUMBER: LSR4B10D010BZ EC4B10209730 4LBMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P210865

CATALOG NUMBER: LSR4B10D010BZ EC4B10209730 4LBMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93						93													
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85						85													
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79						79													
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73						73													
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67						67													
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62						62													
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58						58													
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54						54													
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50						50													
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47						47													

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P210865

CATALOG NUMBER: LSR4B10D010BZ EC4B10209730 4LBMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.0	9.1
10°-20°	144.2	23.9
20°-30°	185.4	30.8
30°-40°	139.5	23.1
40°-50°	56.0	9.3
50°-60°	15.9	2.6
60°-70°	5.0	0.8
70°-80°	1.4	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	384.6	63.8
0°-40°	524.0	87.0
0°-60°	595.9	98.9
0°-90°	602.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	602.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	598	
5°	587	55
15°	515	144
25°	409	185
35°	224	139
45°	69	56
55°	16	16
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P210865

CATALOG NUMBER: LSR4B10D010BZ EC4B10209730 4LBMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	597.5
2.5°	593.9
5°	586.6
7.5°	572.9
10°	555.7
12.5°	534.7
15°	514.7
17.5°	492.0
20°	467.4
22.5°	441.1
25°	409.2
27.5°	371.0
30°	326.5
32.5°	276.5
35°	223.7
37.5°	174.6
40°	131.0
42.5°	96.4
45°	69.1
47.5°	47.3
50°	32.7
52.5°	22.7
55°	16.4
57.5°	11.8
60°	9.1
62.5°	6.4
65°	4.5
67.5°	3.6
70°	2.7
72.5°	1.8
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)