

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211944

Luminaire Tested: **LSR4B30D010BZ EC4B30508030 4LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211944
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30508030 4LBNH1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1823.7 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211944

CATALOG NUMBER: LSR4B30D010BZ EC4B30508030 4LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P211944

CATALOG NUMBER: LSR4B30D010BZ EC4B30508030 4LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																																				
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87																																				
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																																				
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75																																				
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70																																				
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65																																				
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61																																				
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58																																				
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54																																				
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211944

CATALOG NUMBER: LSR4B30D010BZ EC4B30508030 4LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	206.6	11.3
10°-20°	501.1	27.5
20°-30°	581.8	31.9
30°-40°	385.3	21.1
40°-50°	108.1	5.9
50°-60°	27.1	1.5
60°-70°	10.2	0.6
70°-80°	3.5	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1289.6	70.7
0°-40°	1674.9	91.8
0°-60°	1810.1	99.3
0°-90°	1823.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1823.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2290	
5°	2230	207
15°	1794	501
25°	1275	582
35°	618	385
45°	126	108
55°	30	27
65°	10	10
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P211944

CATALOG NUMBER: LSR4B30D010BZ EC4B30508030 4LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2289.8
2.5°	2279.9
5°	2230.3
7.5°	2144.4
10°	2038.7
12.5°	1919.7
15°	1794.2
17.5°	1671.9
20°	1536.5
22.5°	1410.9
25°	1275.4
27.5°	1146.6
30°	981.3
32.5°	806.2
35°	617.9
37.5°	442.8
40°	300.7
42.5°	194.9
45°	125.6
47.5°	76.0
50°	49.6
52.5°	36.3
55°	29.7
57.5°	23.1
60°	16.5
62.5°	13.2
65°	9.9
67.5°	6.6
70°	6.6
72.5°	3.3
75°	3.3
77.5°	3.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)