

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210871

Luminaire Tested: **LSR4B10D010BZ EC4B10209730 4LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210871
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209730 4LBNH1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 500.8 lumens
Efficiency: N/A
Efficacy: 50.6 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210871

CATALOG NUMBER: LSR4B10D010BZ EC4B10209730 4LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P210871

CATALOG NUMBER: LSR4B10D010BZ EC4B10209730 4LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87																			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75																			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70																			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65																			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61																			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58																			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54																			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210871

CATALOG NUMBER: LSR4B10D010BZ EC4B10209730 4LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.7	11.3
10°-20°	137.6	27.5
20°-30°	159.8	31.9
30°-40°	105.8	21.1
40°-50°	29.7	5.9
50°-60°	7.5	1.5
60°-70°	2.8	0.6
70°-80°	0.9	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	354.1	70.7
0°-40°	459.9	91.8
0°-60°	497.1	99.3
0°-90°	500.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	500.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	629	
5°	612	57
15°	493	138
25°	350	160
35°	170	106
45°	34	30
55°	8	7
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P210871

CATALOG NUMBER: LSR4B10D010BZ EC4B10209730 4LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	628.7
2.5°	626.0
5°	612.4
7.5°	588.8
10°	559.8
12.5°	527.1
15°	492.6
17.5°	459.1
20°	421.9
22.5°	387.4
25°	350.2
27.5°	314.8
30°	269.5
32.5°	221.4
35°	169.7
37.5°	121.6
40°	82.6
42.5°	53.5
45°	34.5
47.5°	20.9
50°	13.6
52.5°	10.0
55°	8.2
57.5°	6.4
60°	4.5
62.5°	3.6
65°	2.7
67.5°	1.8
70°	1.8
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)