

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211962

Luminaire Tested: **LSR4B30D010BZ EC4B30509030 4LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211962
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509030 4LBCSMB1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2435.1 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211962

CATALOG NUMBER: LSR4B30D010BZ EC4B30509030 4LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P211962

CATALOG NUMBER: LSR4B30D010BZ EC4B30509030 4LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88																			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75																			
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56																			
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49																			
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43																			
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39																			
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35																			
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31																			
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211962

CATALOG NUMBER: LSR4B30D010BZ EC4B30509030 4LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.3	4.0
10°-20°	277.1	11.4
20°-30°	416.5	17.1
30°-40°	494.2	20.3
40°-50°	489.1	20.1
50°-60°	384.1	15.8
60°-70°	215.4	8.8
70°-80°	60.5	2.5
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	790.8	32.5
0°-40°	1285.1	52.8
0°-60°	2158.3	88.6
0°-90°	2435.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2435.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1028	
5°	1026	97
15°	983	277
25°	904	417
35°	793	494
45°	637	489
55°	433	384
65°	215	215
75°	52	60
85°	0	1
90°	0	



TEST NUMBER: P211962

CATALOG NUMBER: LSR4B30D010BZ EC4B30509030 4LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1028.2
2.5°	1024.7
5°	1026.5
7.5°	1017.8
10°	1007.3
12.5°	995.1
15°	982.9
17.5°	967.1
20°	946.2
22.5°	925.2
25°	904.3
27.5°	881.6
30°	851.9
32.5°	822.2
35°	792.6
37.5°	757.7
40°	717.5
42.5°	679.1
45°	637.2
47.5°	590.1
50°	541.2
52.5°	485.3
55°	432.9
57.5°	373.6
60°	317.7
62.5°	267.1
65°	214.7
67.5°	169.3
70°	125.7
72.5°	85.5
75°	52.4
77.5°	26.2
80°	7.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)