

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210885

Luminaire Tested: **LSR4B10D010BZ EC4B10209730 4LBWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P210885  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B10D010BZ EC4B10209730 4LBWH1  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W  
DL3-11.1W DLE-11.39W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 669.8 lumens  
Efficiency: N/A  
Efficacy: 67.7 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P210885

CATALOG NUMBER: LSR4B10D010BZ EC4B10209730 4LBWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P210885

CATALOG NUMBER: LSR4B10D010BZ EC4B10209730 4LBWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P210885

CATALOG NUMBER: LSR4B10D010BZ EC4B10209730 4LBWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.1	6.1
10°-20°	118.5	17.7
20°-30°	174.8	26.1
30°-40°	172.5	25.8
40°-50°	105.6	15.8
50°-60°	40.5	6.0
60°-70°	12.7	1.9
70°-80°	3.7	0.5
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	334.4	49.9
0°-40°	506.9	75.7
0°-60°	653.0	97.5
0°-90°	669.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	669.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	432	
5°	432	41
15°	420	118
25°	383	175
35°	280	173
45°	135	106
55°	43	40
65°	12	13
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P210885

CATALOG NUMBER: LSR4B10D010BZ EC4B10209730 4LBWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	431.7
2.5°	432.6
5°	431.7
7.5°	430.8
10°	428.1
12.5°	424.5
15°	419.9
17.5°	414.5
20°	406.3
22.5°	397.2
25°	382.6
27.5°	364.5
30°	341.7
32.5°	313.6
35°	279.9
37.5°	242.7
40°	204.5
42.5°	169.1
45°	135.4
47.5°	105.4
50°	80.0
52.5°	59.1
55°	42.7
57.5°	30.0
60°	21.8
62.5°	16.4
65°	11.8
67.5°	9.1
70°	6.4
72.5°	4.5
75°	3.6
77.5°	1.8
80°	1.8
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)