

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210889

Luminaire Tested: **LSR4B10D010BZ EC4B10208035 4LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210889
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10208035 4LBCSMB1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1075.1 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210889

CATALOG NUMBER: LSR4B10D010BZ EC4B10208035 4LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P210889

CATALOG NUMBER: LSR4B10D010BZ EC4B10208035 4LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																			
	1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88																																			
	2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75																																			
	3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65																																			
	4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56																																			
	5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49																																			
	6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43																																			
	7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39																																			
	8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35																																			
	9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31																																			
	10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28																																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210889

CATALOG NUMBER: LSR4B10D010BZ EC4B10208035 4LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.9	4.0
10°-20°	122.3	11.4
20°-30°	183.9	17.1
30°-40°	218.2	20.3
40°-50°	215.9	20.1
50°-60°	169.6	15.8
60°-70°	95.1	8.8
70°-80°	26.7	2.5
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	349.1	32.5
0°-40°	567.3	52.8
0°-60°	952.8	88.6
0°-90°	1075.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1075.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	454	
5°	453	43
15°	434	122
25°	399	184
35°	350	218
45°	281	216
55°	191	170
65°	95	95
75°	23	27
85°	0	0
90°	0	



TEST NUMBER: P210889

CATALOG NUMBER: LSR4B10D010BZ EC4B10208035 4LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	453.9
2.5°	452.4
5°	453.2
7.5°	449.3
10°	444.7
12.5°	439.3
15°	433.9
17.5°	427.0
20°	417.7
22.5°	408.5
25°	399.2
27.5°	389.2
30°	376.1
32.5°	363.0
35°	349.9
37.5°	334.5
40°	316.8
42.5°	299.8
45°	281.3
47.5°	260.5
50°	238.9
52.5°	214.3
55°	191.1
57.5°	164.9
60°	140.3
62.5°	117.9
65°	94.8
67.5°	74.8
70°	55.5
72.5°	37.8
75°	23.1
77.5°	11.6
80°	3.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)