

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211989

Luminaire Tested: **LSR4B30D010BZ EC4B30509030 4LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211989
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509030 4LBWMW1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2176.6 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211989

CATALOG NUMBER: LSR4B30D010BZ EC4B30509030 4LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P211989

CATALOG NUMBER: LSR4B30D010BZ EC4B30509030 4LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78																			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69																			
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61																			
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55																			
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50																			
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45																			
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41																			
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38																			
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211989

CATALOG NUMBER: LSR4B30D010BZ EC4B30509030 4LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.8	5.7
10°-20°	346.3	15.9
20°-30°	489.4	22.5
30°-40°	474.1	21.8
40°-50°	319.9	14.7
50°-60°	198.6	9.1
60°-70°	132.7	6.1
70°-80°	72.6	3.3
80°-90°	19.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	959.6	44.1
0°-40°	1433.7	65.9
0°-60°	1952.1	89.7
0°-90°	2176.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2176.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1319	
5°	1308	124
15°	1229	346
25°	1073	489
35°	763	474
45°	410	320
55°	218	199
65°	133	133
75°	68	73
85°	17	19
90°	0	



TEST NUMBER: P211989

CATALOG NUMBER: LSR4B30D010BZ EC4B30509030 4LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1319.0
2.5°	1319.0
5°	1307.7
7.5°	1293.5
10°	1276.6
12.5°	1259.6
15°	1228.6
17.5°	1203.2
20°	1160.8
22.5°	1118.4
25°	1073.2
27.5°	1011.1
30°	943.3
32.5°	855.8
35°	762.6
37.5°	669.4
40°	576.2
42.5°	483.0
45°	409.5
47.5°	341.7
50°	290.9
52.5°	248.5
55°	217.5
57.5°	192.1
60°	172.3
62.5°	152.5
65°	132.7
67.5°	115.8
70°	98.9
72.5°	84.7
75°	67.8
77.5°	53.7
80°	39.5
82.5°	28.2
85°	16.9
87.5°	5.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)