

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212003

Luminaire Tested: **LSR4B30D010BZ EC4B30509730 4LBNI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212003
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509730 4LBNI1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1603.6 lumens
Efficiency: N/A
Efficacy: 57.3 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212003

CATALOG NUMBER: LSR4B30D010BZ EC4B30509730 4LBNLI1

Luminous Intensity Polar Plot





TEST NUMBER: P212003

CATALOG NUMBER: LSR4B30D010BZ EC4B30509730 4LBNLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95									95																			
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90									90																			
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85									85																			
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81									81																			
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77									77																			
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73									73																			
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69									69																			
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66									66																			
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63									63																			
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61									61																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212003

CATALOG NUMBER: LSR4B30D010BZ EC4B30509730 4LBNLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	325.2	20.3
10°-20°	556.8	34.7
20°-30°	442.5	27.6
30°-40°	234.2	14.6
40°-50°	40.4	2.5
50°-60°	3.0	0.2
60°-70°	1.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1324.5	82.6
0°-40°	1558.7	97.2
0°-60°	1602.1	99.9
0°-90°	1603.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1603.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4127	
5°	3700	325
15°	2013	557
25°	953	443
35°	370	234
45°	42	40
55°	2	3
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P212003

CATALOG NUMBER: LSR4B30D010BZ EC4B30509730 4LBNLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	4126.8
2.5°	4020.6
5°	3699.5
7.5°	3279.7
10°	2835.1
12.5°	2405.4
15°	2012.8
17.5°	1647.2
20°	1355.8
22.5°	1133.6
25°	953.3
27.5°	807.6
30°	661.9
32.5°	513.7
35°	370.4
37.5°	244.5
40°	145.7
42.5°	84.0
45°	42.0
47.5°	14.8
50°	4.9
52.5°	4.9
55°	2.5
57.5°	2.5
60°	2.5
62.5°	2.5
65°	2.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)