

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212013

Luminaire Tested: **LSR4B30D010BZ EC4B30509730 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212013
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509730 4LBSWMH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3038.3 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212013

CATALOG NUMBER: LSR4B30D010BZ EC4B30509730 4LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P212013

CATALOG NUMBER: LSR4B30D010BZ EC4B30509730 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212013

CATALOG NUMBER: LSR4B30D010BZ EC4B30509730 4LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.0	5.9
10°-20°	471.6	15.5
20°-30°	633.4	20.8
30°-40°	648.4	21.3
40°-50°	561.2	18.5
50°-60°	373.3	12.3
60°-70°	153.3	5.0
70°-80°	18.2	0.6
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1283.0	42.2
0°-40°	1931.4	63.6
0°-60°	2865.9	94.3
0°-90°	3038.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3038.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1926	
5°	1896	178
15°	1685	472
25°	1382	633
35°	1036	648
45°	731	561
55°	414	373
65°	151	153
75°	8	18
85°	0	1
90°	0	



TEST NUMBER: P212013

CATALOG NUMBER: LSR4B30D010BZ EC4B30509730 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1925.6
2.5°	1921.6
5°	1895.8
7.5°	1855.9
10°	1802.2
12.5°	1742.4
15°	1684.7
17.5°	1611.0
20°	1539.3
22.5°	1463.6
25°	1382.0
27.5°	1294.4
30°	1206.7
32.5°	1119.1
35°	1035.5
37.5°	955.8
40°	880.2
42.5°	804.5
45°	730.8
47.5°	653.2
50°	573.5
52.5°	493.9
55°	414.2
57.5°	344.5
60°	272.8
62.5°	207.1
65°	151.3
67.5°	99.6
70°	57.7
72.5°	27.9
75°	8.0
77.5°	4.0
80°	2.0
82.5°	2.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)