

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210913

Luminaire Tested: **LSR4B10D010BZ EC4B10208035 4LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210913
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10208035 4LBWGPH1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 720.0 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210913

CATALOG NUMBER: LSR4B10D010BZ EC4B10208035 4LBWGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P210913

CATALOG NUMBER: LSR4B10D010BZ EC4B10208035 4LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92			
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76			
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57			
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53			
8	73	62	56	51	72	62	55	51	61	55	51	59	54	50	58	54	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	42			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210913

CATALOG NUMBER: LSR4B10D010BZ EC4B10208035 4LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.9	6.8
10°-20°	138.5	19.2
20°-30°	198.7	27.6
30°-40°	187.1	26.0
40°-50°	103.3	14.3
50°-60°	33.1	4.6
60°-70°	8.3	1.1
70°-80°	1.9	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	386.1	53.6
0°-40°	573.2	79.6
0°-60°	709.6	98.6
0°-90°	720.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	720.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	518	
5°	516	49
15°	491	139
25°	436	199
35°	304	187
45°	131	103
55°	34	33
65°	8	8
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P210913

CATALOG NUMBER: LSR4B10D010BZ EC4B10208035 4LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	518.3
2.5°	514.5
5°	515.8
7.5°	512.0
10°	505.8
12.5°	499.5
15°	490.8
17.5°	483.3
20°	470.8
22.5°	453.3
25°	435.8
27.5°	412.1
30°	380.9
32.5°	345.9
35°	303.5
37.5°	258.5
40°	212.3
42.5°	169.8
45°	131.1
47.5°	98.7
50°	71.2
52.5°	50.0
55°	33.7
57.5°	22.5
60°	16.2
62.5°	11.2
65°	7.5
67.5°	5.0
70°	3.7
72.5°	2.5
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)