

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210924

Luminaire Tested: **LSR4B10D010BZ EC4B10209035 4LBMLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P210924  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B10D010BZ EC4B10209035 4LBML1  
Description: PORTFOLIO 4 INCH CYLINDER  
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W  
DL3-11.1W DLE-11.39W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 873.0 lumens  
Efficiency: N/A  
Efficacy: 88.2 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P210924

CATALOG NUMBER: LSR4B10D010BZ EC4B10209035 4LBML11

### Luminous Intensity Polar Plot





TEST NUMBER: P210924

CATALOG NUMBER: LSR4B10D010BZ EC4B10209035 4LBML11

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88																			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83																			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78																			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73																			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	70	69																			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65																			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62																			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58																			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P210924

CATALOG NUMBER: LSR4B10D010BZ EC4B10209035 4LBML11

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.6	14.3
10°-20°	278.6	31.9
20°-30°	277.0	31.7
30°-40°	150.8	17.3
40°-50°	34.8	4.0
50°-60°	4.9	0.6
60°-70°	1.8	0.2
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	680.1	77.9
0°-40°	831.0	95.2
0°-60°	870.7	99.7
0°-90°	873.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	873.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1376	
5°	1348	125
15°	1006	279
25°	607	277
35°	233	151
45°	40	35
55°	5	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P210924

CATALOG NUMBER: LSR4B10D010BZ EC4B10209035 4LBML11

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1376.2
2.5°	1373.1
5°	1347.7
7.5°	1296.0
10°	1224.1
12.5°	1118.5
15°	1005.5
17.5°	893.6
20°	783.7
22.5°	693.9
25°	607.3
27.5°	524.9
30°	432.0
32.5°	328.5
35°	233.4
37.5°	157.4
40°	102.5
42.5°	64.4
45°	40.1
47.5°	23.2
50°	11.6
52.5°	6.3
55°	5.3
57.5°	3.2
60°	3.2
62.5°	2.1
65°	2.1
67.5°	1.1
70°	1.1
72.5°	1.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)