

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212029

Luminaire Tested: **LSR4B30D010BZ EC4B30508035 4LBNB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212029  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B30D010BZ EC4B30508035 4LBNB1  
Description: PORTFOLIO 4 INCH CYLINDER  
NARROW DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1160.0 lumens  
Efficiency: N/A  
Efficacy: 41.4 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.79  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212029

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBNB1

### Luminous Intensity Polar Plot





TEST NUMBER: P212029

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBNB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																												
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88																												
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83																												
4	99	92	86	82	97	90	86	82	88	84	81	86	83	80	85	82	79	78																												
5	94	86	81	77	92	85	80	76	84	79	76	82	78	75	80	77	74	73																												
6	90	81	76	72	88	81	75	71	79	74	71	78	74	70	76	73	70	69																												
7	86	77	71	67	84	76	71	67	75	70	67	74	69	66	73	69	66	65																												
8	82	73	67	63	80	72	67	63	71	66	63	70	66	62	69	65	62	61																												
9	78	69	63	60	77	68	63	59	67	63	59	67	62	59	66	62	59	58																												
10	75	65	60	56	74	65	60	56	64	59	56	63	59	56	63	59	56	54																												

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212029

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBNB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.0	13.6
10°-20°	335.2	28.9
20°-30°	388.9	33.5
30°-40°	243.5	21.0
40°-50°	34.3	3.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	882.2	76.0
0°-40°	1125.7	97.0
0°-60°	1160.0	100.0
0°-90°	1160.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1160.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1897	
5°	1758	158
15°	1191	335
25°	858	389
35°	390	244
45°	30	34
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P212029

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBNB1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1896.8
2.5°	1859.5
5°	1757.7
7.5°	1611.8
10°	1462.5
12.5°	1320.0
15°	1191.0
17.5°	1082.4
20°	1001.0
22.5°	926.3
25°	858.5
27.5°	777.0
30°	671.9
32.5°	539.5
35°	390.2
37.5°	254.5
40°	145.9
42.5°	74.7
45°	30.5
47.5°	6.8
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)