

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210935

Luminaire Tested: **LSR4B10D010BZ EC4B10209035 4LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210935
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209035 4LBSGPH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 838.6 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210935

CATALOG NUMBER: LSR4B10D010BZ EC4B10209035 4LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P210935

CATALOG NUMBER: LSR4B10D010BZ EC4B10209035 4LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210935

CATALOG NUMBER: LSR4B10D010BZ EC4B10209035 4LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.7	4.4
10°-20°	102.9	12.3
20°-30°	150.1	17.9
30°-40°	171.2	20.4
40°-50°	164.2	19.6
50°-60°	125.8	15.0
60°-70°	69.0	8.2
70°-80°	18.4	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	289.7	34.6
0°-40°	460.9	55.0
0°-60°	751.0	89.6
0°-90°	838.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	838.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	390	
5°	386	37
15°	365	103
25°	326	150
35°	274	171
45°	213	164
55°	141	126
65°	69	69
75°	16	18
85°	0	0
90°	0	



TEST NUMBER: P210935

CATALOG NUMBER: LSR4B10D010BZ EC4B10209035 4LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	389.5
2.5°	388.5
5°	386.5
7.5°	383.4
10°	379.4
12.5°	372.4
15°	365.3
17.5°	357.3
20°	348.2
22.5°	337.2
25°	326.1
27.5°	315.0
30°	300.9
32.5°	287.8
35°	273.7
37.5°	259.7
40°	245.6
42.5°	230.5
45°	213.4
47.5°	196.3
50°	178.1
52.5°	159.0
55°	140.9
57.5°	122.8
60°	103.7
62.5°	85.5
65°	69.4
67.5°	53.3
70°	39.3
72.5°	26.2
75°	16.1
77.5°	7.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)