

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212044

Luminaire Tested: **LSR4B30D010BZ EC4B30508035 4LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212044
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30508035 4LBWGPH1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1957.1 lumens
Efficiency: N/A
Efficacy: 69.9 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212044

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBWGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P212044

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92			
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76			
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57			
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53			
8	73	62	56	51	72	62	55	51	61	55	51	59	54	50	58	54	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212044

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.9	6.8
10°-20°	376.6	19.2
20°-30°	540.0	27.6
30°-40°	508.5	26.0
40°-50°	280.8	14.3
50°-60°	90.1	4.6
60°-70°	22.5	1.2
70°-80°	5.4	0.3
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1049.4	53.6
0°-40°	1557.9	79.6
0°-60°	1928.7	98.6
0°-90°	1957.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1957.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1409	
5°	1402	133
15°	1334	377
25°	1185	540
35°	825	508
45°	356	281
55°	92	90
65°	20	23
75°	3	5
85°	0	0
90°	0	



TEST NUMBER: P212044

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1408.6
2.5°	1398.4
5°	1401.8
7.5°	1391.7
10°	1374.7
12.5°	1357.7
15°	1334.0
17.5°	1313.6
20°	1279.6
22.5°	1232.1
25°	1184.6
27.5°	1120.1
30°	1035.3
32.5°	940.2
35°	824.8
37.5°	702.6
40°	577.0
42.5°	461.6
45°	356.4
47.5°	268.1
50°	193.5
52.5°	135.8
55°	91.6
57.5°	61.1
60°	44.1
62.5°	30.5
65°	20.4
67.5°	13.6
70°	10.2
72.5°	6.8
75°	3.4
77.5°	3.4
80°	3.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)