

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212048

Luminaire Tested: **LSR4B30D010BZ EC4B30508035 4LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212048
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30508035 4LBWWH1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2594.8 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212048

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P212048

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92																			
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84																			
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76																			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69																			
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63																			
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58																			
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53																			
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49																			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45																			
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212048

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.2	6.1
10°-20°	486.3	18.7
20°-30°	748.0	28.8
30°-40°	721.8	27.8
40°-50°	376.3	14.5
50°-60°	79.2	3.1
60°-70°	18.4	0.7
70°-80°	7.2	0.3
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1391.5	53.6
0°-40°	2113.3	81.4
0°-60°	2568.8	99.0
0°-90°	2594.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2594.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1622	
5°	1636	157
15°	1721	486
25°	1639	748
35°	1171	722
45°	479	376
55°	71	79
65°	17	18
75°	7	7
85°	0	0
90°	0	



TEST NUMBER: P212048

CATALOG NUMBER: LSR4B30D010BZ EC4B30508035 4LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1622.4
2.5°	1625.8
5°	1636.0
7.5°	1649.5
10°	1669.9
12.5°	1697.1
15°	1720.8
17.5°	1734.4
20°	1724.2
22.5°	1703.8
25°	1639.4
27.5°	1561.3
30°	1459.5
32.5°	1323.7
35°	1171.0
37.5°	1004.7
40°	831.6
42.5°	658.5
45°	478.6
47.5°	322.4
50°	207.0
52.5°	125.6
55°	71.3
57.5°	44.1
60°	30.5
62.5°	23.8
65°	17.0
67.5°	13.6
70°	10.2
72.5°	10.2
75°	6.8
77.5°	3.4
80°	3.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)