

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212054

Luminaire Tested: **LSR4B30D010BZ EC4B30509035 4LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212054
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B30D010BZ EC4B30509035 4LBMH1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1901.0 lumens
Efficiency: N/A
Efficacy: 67.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212054

CATALOG NUMBER: LSR4B30D010BZ EC4B30509035 4LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P212054

CATALOG NUMBER: LSR4B30D010BZ EC4B30509035 4LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85																			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79																			
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73																			
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67																			
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62																			
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58																			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54																			
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50																			
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212054

CATALOG NUMBER: LSR4B30D010BZ EC4B30509035 4LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.5	9.1
10°-20°	455.0	23.9
20°-30°	584.8	30.8
30°-40°	440.0	23.1
40°-50°	176.7	9.3
50°-60°	50.2	2.6
60°-70°	15.9	0.8
70°-80°	4.5	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1213.3	63.8
0°-40°	1653.3	87.0
0°-60°	1880.2	98.9
0°-90°	1901.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1901.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1885	
5°	1851	173
15°	1624	455
25°	1291	585
35°	706	440
45°	218	177
55°	52	50
65°	14	16
75°	3	5
85°	0	0
90°	0	



TEST NUMBER: P212054

CATALOG NUMBER: LSR4B30D010BZ EC4B30509035 4LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1885.0
2.5°	1873.5
5°	1850.6
7.5°	1807.5
10°	1753.0
12.5°	1687.0
15°	1623.9
17.5°	1552.2
20°	1474.7
22.5°	1391.5
25°	1291.1
27.5°	1170.6
30°	1030.0
32.5°	872.2
35°	705.8
37.5°	550.9
40°	413.1
42.5°	304.1
45°	218.1
47.5°	149.2
50°	103.3
52.5°	71.7
55°	51.6
57.5°	37.3
60°	28.7
62.5°	20.1
65°	14.3
67.5°	11.5
70°	8.6
72.5°	5.7
75°	2.9
77.5°	2.9
80°	2.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)