

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211013

Luminaire Tested: **LSR4B10D010BZ EC4B10208050 4LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211013
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10208050 4LBMWH1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 854.1 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211013

CATALOG NUMBER: LSR4B10D010BZ EC4B10208050 4LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P211013

CATALOG NUMBER: LSR4B10D010BZ EC4B10208050 4LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	111	108	106	111	109	106	105	105	103	101	101	100	98	98	96	95	94																												
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87																												
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81																												
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76																												
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71																												
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66																												
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62																												
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58																												
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55																												
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211013

CATALOG NUMBER: LSR4B10D010BZ EC4B10208050 4LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.7	11.0
10°-20°	240.9	28.2
20°-30°	282.7	33.1
30°-40°	178.9	20.9
40°-50°	47.9	5.6
50°-60°	6.7	0.8
60°-70°	2.5	0.3
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	617.3	72.3
0°-40°	796.2	93.2
0°-60°	850.8	99.6
0°-90°	854.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	854.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1014	
5°	998	94
15°	863	241
25°	624	283
35°	284	179
45°	54	48
55°	6	7
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P211013

CATALOG NUMBER: LSR4B10D010BZ EC4B10208050 4LBMWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1014.4
2.5°	1010.6
5°	998.0
7.5°	977.8
10°	948.8
12.5°	910.9
15°	863.0
17.5°	813.8
20°	754.5
22.5°	693.9
25°	624.5
27.5°	548.8
30°	464.3
32.5°	372.2
35°	283.9
37.5°	205.7
40°	141.3
42.5°	90.8
45°	54.3
47.5°	30.3
50°	16.4
52.5°	8.8
55°	6.3
57.5°	5.0
60°	3.8
62.5°	3.8
65°	2.5
67.5°	1.3
70°	1.3
72.5°	1.3
75°	1.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)