

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211022

Luminaire Tested: **LSR4B10D010BZ EC4B10208050 4LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211022
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10208050 4LBSGPH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1002.3 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211022

CATALOG NUMBER: LSR4B10D010BZ EC4B10208050 4LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P211022

CATALOG NUMBER: LSR4B10D010BZ EC4B10208050 4LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88																			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76																			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66																			
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57																			
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50																			
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45																			
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32																			
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211022

CATALOG NUMBER: LSR4B10D010BZ EC4B10208050 4LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.8	4.4
10°-20°	123.0	12.3
20°-30°	179.4	17.9
30°-40°	204.6	20.4
40°-50°	196.3	19.6
50°-60°	150.3	15.0
60°-70°	82.5	8.2
70°-80°	21.9	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	346.3	34.6
0°-40°	550.9	55.0
0°-60°	897.5	89.5
0°-90°	1002.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1002.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	466	
5°	462	44
15°	437	123
25°	390	179
35°	327	205
45°	255	196
55°	168	150
65°	83	82
75°	19	22
85°	0	0
90°	0	



TEST NUMBER: P211022

CATALOG NUMBER: LSR4B10D010BZ EC4B10208050 4LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	465.5
2.5°	464.3
5°	461.9
7.5°	458.3
10°	453.5
12.5°	445.1
15°	436.6
17.5°	427.0
20°	416.2
22.5°	403.0
25°	389.7
27.5°	376.5
30°	359.7
32.5°	344.0
35°	327.2
37.5°	310.3
40°	293.5
42.5°	275.5
45°	255.0
47.5°	234.6
50°	212.9
52.5°	190.1
55°	168.4
57.5°	146.7
60°	123.9
62.5°	102.2
65°	83.0
67.5°	63.8
70°	46.9
72.5°	31.3
75°	19.2
77.5°	8.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)