

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211033

Luminaire Tested: **LSR4B10D010BZ EC4B10208050 4LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211033  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B10D010BZ EC4B10208050 4LBWWH1  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W  
DL3-11.1W DLE-11.39W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 965.1 lumens  
Efficiency: N/A  
Efficacy: 97.5 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211033

CATALOG NUMBER: LSR4B10D010BZ EC4B10208050 4LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P211033

CATALOG NUMBER: LSR4B10D010BZ EC4B10208050 4LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92															
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84				84															
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76				76															
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69															
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63															
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58				58															
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53				53															
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49				49															
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45				45															
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41				41															

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211033

CATALOG NUMBER: LSR4B10D010BZ EC4B10208050 4LBWWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.5	6.1
10°-20°	180.9	18.7
20°-30°	278.2	28.8
30°-40°	268.5	27.8
40°-50°	140.0	14.5
50°-60°	29.5	3.1
60°-70°	6.8	0.7
70°-80°	2.7	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	517.6	53.6
0°-40°	786.0	81.4
0°-60°	955.5	99.0
0°-90°	965.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	965.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	604	
5°	608	58
15°	640	181
25°	610	278
35°	436	268
45°	178	140
55°	26	29
65°	6	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P211033

CATALOG NUMBER: LSR4B10D010BZ EC4B10208050 4LBWWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	603.5
2.5°	604.7
5°	608.5
7.5°	613.6
10°	621.1
12.5°	631.2
15°	640.1
17.5°	645.1
20°	641.3
22.5°	633.8
25°	609.8
27.5°	580.7
30°	542.9
32.5°	492.4
35°	435.5
37.5°	373.7
40°	309.3
42.5°	244.9
45°	178.0
47.5°	119.9
50°	77.0
52.5°	46.7
55°	26.5
57.5°	16.4
60°	11.4
62.5°	8.8
65°	6.3
67.5°	5.0
70°	3.8
72.5°	3.8
75°	2.5
77.5°	1.3
80°	1.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)